

□□□

□□□□□□□□□□

4mil □□□□□

640\*480 CMOS Sensor

□□□□□□□□

□□□

□□□	
□□	OCBS-T2 18
□□	USB
□□□□	5V
□□□□	315□□
□□ □□	320□□
□□□□	235□□
□□□□	□□□ 120 □□□□□□□□
□□	
□□□	CMOS 640*480 □□
□□	□□□□□□□ LED□□□□□□□ LED
□□	39 ° □□□□x29 ° □□□□
□□□	>/= 400 □
□□□□	□□ ±6.5 °@ 0°Roll □ 0° Skew
□□□□	□□ 360 ° @ 0 ° □□□ 0 ° □□
□□□□	□□ ± 6.5 ° @ 0 ° Roll □ 0 ° Pitch
□□□□	20% □□□□□
□□□□□	0-100,000 □□□
□□□□	Code39(5mil):0mm-70mm,Code39(13mil):0mm-170mm
□□□□	□□□(20mil):0mm-110mm,□□□(□□□30mm*30mm):0mm-300mm
□□□□	1D□ Codabar □ Code 39 □ Code 32 Pharmaceutical (PARAF) □
□□□□	Interleaved 2 of 5,NEC 2 of 5,Code 93,Straight 2 of 5 Industrial,Straight 2 of 5 IATA,Matrix 2 of 5,Code 11,Code 128,GS1-128,UPC-A,UPC-E, EAN/JAN-8,EAN/JAN-13,MSI,GS1 DataBar Omnidirectional,GS1 DataBar Limited,GS1 DataBar Expanded,China Post(Hong Kong 2 of 5),Korea Post
□□□□	2D□ DO T□□□□□□□-A □□□□-F □ PDF417 □ MicroPDF417 □
□□□□	GS1□□□□□□□□□□Data Matrix□MaxiCode□Aztec□HANXIN
□□□□	Codabar,Code39,Interleaved2of5,NEC2of5,Code93,Code128,GS1-128,UPC-A,UPC-E0,EAN/JAN-13,EAN/JAN-8,GS1-DataBar,PDF417,QR,DM,Aztec
□□	
□□	□□□249□
□□	140.2 * 84 * 90.1□□
□□	
□□□□□□□	0□45□□□□10%~80%□□□
□□□□□□□	-20 □ 60 □□□□10%~90% □□□









